Loose Water Hammer Arresters

Product Specifications



FDA/NSF Approved Materials:

- · Acetal outer shell and piston
- CPVC outer shell for ML45MIP and ML45CPM
- · Buna N O-rings
- · FDA approved silicone lubrication

Working parameters:

- Max Working Temp: 180°
- Max Working Pressure: 170 PSIGBurst Tested to up: 1,200 PSIG

Installation:

- · Arrester may be installed at any angle
- · All ML45 models are approved for in-wall installations
- · No access panel is required
- Use pipe dope only on 1/2" MIP

Listings:

- IAPMO: Uniform Plumbing Code
- ASSE: ANSI/ASSE 1010-2004
- NSF 61
- · Meets all low lead requirements

Attachments:

Permanent Factory Seal



AcetalShell

Pressure chamber

silicone lubricant

Acetal piston with dual Buna N

O-rings and FDA approved

✓ To Submit	Part #	Connection
	ML45MIP	1/2" MIP
	ML45CPM	1/2" CPVC
	ML45PEX	1/2" PEX Poly Barb
	ML45UPW	1/2" UPONOR/Wirsbo, F1960 PEX
	ML45DCT	3/8" OD x 3/8" Comp, Dish Washer
	ML45PXT	1/2" PEX Poly Barb Tee
	ML45UPWT	1/2" UPONOR/Wirsbo Tee, F1960 PEX









Warranty

See warranty information for more details.

All dimensions listed are nominal. MAINLINE® reserves the right to make product and material changes at any time without notice.